

**Garant**

**eco blade carrier, concave for face grooving, left-hand, Ø range Groove D1 / D2: 67/100mm**


**Order data**

Order number	273891 67/100
GTIN	4045197516749
Item class	21W

**Description**
**Application:**

In conjunction with GARANT eco-toolholder No. **273840 – 273851**.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

$D_1$  = minimum  $\varnothing$  for the first first groove /  $D_2$  = minimum  $\varnothing$  for the second groove.

Through-coolant: yes

Groove width w: 3 mm

maximum cutting depth  $t_{max}$ : 13 mm

Clamping screw: 279815 9

**Technical description**

maximum cutting depth $t_{max}$	13 mm
maximum 1st groove $\varnothing D_2$	100 mm
minimum 1st groove $\varnothing D_1$	67 mm
Series	Eco
Clamping screw	279815 9

Application type	left-hand
Through-coolant	yes
Groove width w	3 mm
Type of product	Cartridges

---

## Accessories

Clamping screw Type 9	279815 9
Clamping screw	279910