

Garant**Screw-on toolholder, left-hand, Shank / insert size: 16/11mm****Order data**

Order number	261309 16/11
GTIN	4045197655929
Item class	21T

Technical description

Functional width L ₄	20 mm
Shank size	16 mm
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 22
ISO code toolholder	SVHCR/L 1616H11
Head length L ₁	13 mm
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500