

Garant**Screw-on toolholder, right-hand, Shank / insert size: 12/11 mm****Order data**

Order number	261308 12/11
GTIN	4045197655882
Item class	21T

Technical description

Shank size	12 mm
Head length L ₁	13 mm
suitable indexable insert	VC.. 1103..
ISO code toolholder	SVHCR/L 1212F11
Pack of insert screws	269028 22
Functional width L ₄	16 mm
Insert size	11 mm
Overall length L	80 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500