

**Garant**
**Screw-on toolholder, right-hand, Shank / insert size: 20/11 mm**

**Order data**

Order number	261308 20/11
GTIN	4045197655905
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	25 mm
Shank size	20 mm
ISO code toolholder	SVHCR/L 2020K11
Head length L <sub>1</sub>	17 mm
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 22
Overall length L	125 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500