

Garant
Screw-on toolholder, right-hand, Shank / insert size: 25/11 mm


Order data

Order number	261312 25/11
GTIN	4045197653833
Item class	21T

Technical description

ISO code toolholder	SVJCR/L 2525M11
Pack of insert screws	269028 22
Insert size	11 mm
Shank size	25 mm
suitable indexable insert	VC.. 1103..
Functional width L ₄	32 mm
Head length L ₁	26 mm
Overall length L	150 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500