

**Garant**
**Side lock arbor Form AD, SK 40 ultra short, Clamping range  $\varnothing$  D1: 25mm**

**Order data**

Order number	300410 25
GTIN	4045197284365
Item class	31A

**Description**
**Version:**

With only a single shorter locking screw.

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Standard:**

Ähnlich DIN 69871.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820; 308830, spare screw No. 309901.

**Technical description**

Overhang dimension A	60 mm
Clamping $\varnothing$ D <sub>1</sub>	25 mm
External $\varnothing$ D	65 mm
Adapter	SK 40 ultra short
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 µm
Type of product	Side lock arbor

## Accessories

Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Clamping screw for Weldon arbor ultra short for chuck clamping Ø D1 25 mm	309901 25
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studsealed suitable for steep tapers 40	308660 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
	308615 40

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40

Pull stud 60°sealed suitable for steep tapers 40

308785 40

Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40

308820 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

308630 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

308801 40

Pull stud 45°sealed suitable for steep tapers 40

308765 40