

LOCTITE.**Instant adhesive, 20 g, Manufacturer ID: 454**

Order data

Order number	083352 454
GTIN	5010266454160
Item class	04L

Description

Version:

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity.

Application:

Universal instant adhesive **gel**. Suitable for **virtually all materials**. Non-drip, ideal for applications on vertical surfaces or overhead.

Note:

Not available in all countries. Express delivery not possible.

Technical description

Manufacturer's designation	LOCTITE 454
Tensile shear strength	20.9 N/mm ²
Touch dry after	5 - 10 s
Labelling of hazardous substances	GHS07: Exclamation mark
Dynamic viscosity	150 - 450 mPas

Storage temperature	2 °C
Working life after date of manufacture	24 mo
Colour	transparent
Suitable for material	Leather
Suitable for material	Metal
Suitable for material	Paper
Suitable for material	wood
Suitable for material	Plastic
Suitable for material	cardboard
Suitable for material	Elastomer
Suitable for material	porous materials
Characteristics	anaerobic adhesive
Characteristics	does not penetrate into workpiece surface
Operating temperature range	-40 °C
Shape	Gel
Chemical basis	Ethyl cyanoacrylate
Density	1.05 g/cm ³
Capacity	20 ml
Maximum gap size	0.15 mm
Product name attribute	20 g
Type of product	Instant adhesive