

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 25/16mm

Order data

Order number	261331 25/16
GTIN	4045197654007
Item class	21T

Technical description

Insert size	16 mm
Head length L_1	44 mm
Centre offset L_3	3.5 mm
ISO code toolholder	AH25R SVJCR/L16
suitable indexable insert	VC.. 1604..
Neck width L_4	14.5 mm
Pack of insert screws	269028 8
Minimum pre-drill $\varnothing D_{\min}$	28 mm
Overall length L	200 mm
Clamping height L_2	24 mm
Setting angle κ	142 degrees
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500