

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 16/11 mm

Order data

Order number	261334 16/11
GTIN	4045197654014
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	21 mm
ISO code toolholder	AH16Q SVUCR/L11
Centre offset L_3	11 mm
Pack of insert screws	269028 7
Head length L_1	20 mm
suitable indexable insert	VC.. 1103..
Insert size	11 mm
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500