

**Garant**
**Combination side lock arbor, slim Form ADB, SK 40 A = 100, Clamping range  
 Ø D1: 14mm**

**Order data**

Order number	300422 14
GTIN	4045197287649
Item class	31A

**Description**
**Version:**

- **Hole tolerance D<sub>1</sub> in H4 (tighter than DIN).**

Shanks hard turned (smooth cutting action!). With RFID/Balluffchip bore.

**Application:**

For clamping tools with plain shank to DIN 1835 Form B + E and DIN 6535 Form HB + HE.

**Supplied with:**

With ball-jointed clamping screw **for Weldon and Whistle Notch systems** and through drilled back stop screw.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No. 308820 – 308835, spare clamping screw 309905 M6, 309905 M8.

**Technical description**

Ø D <sub>2</sub>	19 mm
Ø D <sub>3</sub>	24 mm
Overhang dimension A	100 mm
Clamping Ø D <sub>1</sub>	14 mm
External Ø D	36.22 mm
Adapter	SK 40 A = 100

Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studForm A suitable for steep tapers 40	308600 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studsealed, form B suitable for steep tapers 40	308650 40

Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40