

**Garant**
**Whistle Notch arbor Form ADB, SK 40 short, Clamping range  $\varnothing$  D1: 16mm**

**Order data**

Order number	300430 16
GTIN	4045197284457
Item class	31A

**Description**
**Version:**

With back stop screw. Shanks hard turned (smooth cutting action!). With RFID/Balluffchip bore.

**Advantage:**

The tool is firmly clamped at the side with the clamping screw and supported at the back with the back stop screw. Clamping free of play, giving low vibration running.

**Application:**

For clamping tools with parallel shank **and whistle notch shanks** (2°) to DIN 1835 E and DIN 6535 HE.

- **The loss of length due to regrinding of the drill front can be corrected by axial length adjustment in the toolholder.**

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

Overhang dimension A	63 mm
Spare clamping screw No. 30 9900	16
Clamping $\varnothing$ D <sub>1</sub>	16 mm
External $\varnothing$ D	48 mm
Adapter	SK 40 short
Standard	DIN 6359

Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studsealed suitable for steep tapers 40	308660 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40

Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Spare clamping screw for chucks with clamping Ø D1 16 mm	309900 16