

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

| | |
|--------------|---------------|
| Order number | 261335 16/11 |
| GTIN | 4045197654045 |
| Item class | 21T |

Technical description

| | |
|--|-------------------------------|
| Centre offset L_3 | 11 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 21 mm |
| Insert size | 11 mm |
| suitable indexable insert | VC.. 1103.. |
| Head length L_1 | 20 mm |
| Pack of insert screws | 269028 7 |
| ISO code toolholder | AH16Q SVUCR/L11 |
| Overall length L | 180 mm |
| Clamping height L_2 | 15 mm |
| Setting angle κ | 93 degrees |
| Shank $\varnothing D_s$ | 16 mm |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 5xD |
| Tool material | HSS |
| Through-coolant | yes |
| Application | Internal longitudinal turning |

| | |
|-----------------|------------|
| Type of product | Boring bar |
|-----------------|------------|

Accessories

| | |
|--|------------|
| Set of insert screws Type 7 | 269028 7 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |