

**Garant**
**Boring bar HSS, right-hand, Shank Ø / insert size: 20/11 mm**

**Order data**

Order number	261330 20/11
GTIN	4045197653963
Item class	21T

**Technical description**

Insert size	11 mm
Head length L <sub>1</sub>	38 mm
Neck width L <sub>4</sub>	12 mm
ISO code toolholder	AH20Q SVJCR/L11
suitable indexable insert	VC.. 1103..
Centre offset L <sub>3</sub>	4.6 mm
Minimum pre-drill Ø D <sub>min</sub>	25 mm
Pack of insert screws	269028 7
Overall length L	180 mm
Clamping height L <sub>2</sub>	19 mm
Setting angle κ	142 degrees
Shank Ø D <sub>s</sub>	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500