

Garant
Side lock arbor Form AD, SK 40 ultra short, Clamping range \varnothing D1: 20mm

Order data

Order number	300410 20
GTIN	4045197284358
Item class	31A

Description
Version:

Locking screw in tool gripper groove.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Standard:

Ähnlich DIN 69871.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820; 308830, spare screw No. 309901.

Technical description

Clamping \varnothing D ₁	20 mm
Overhang dimension A	40 mm
External \varnothing D	50 mm
Adapter	SK 40 ultra short
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Type of product	Side lock arbor

Accessories

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40

Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull studForm B suitable for steep tapers 40	308640 40
Clamping screw for Weldon arbor ultra short for chuck clamping Ø D1 20 mm	309901 20
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40