

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 20/11mm


Order data

| | |
|--------------|---------------|
| Order number | 261338 20/11 |
| GTIN | 4045197654083 |
| Item class | 21T |

Technical description

| | |
|-------------------------------|-------------------------------|
| suitable indexable insert | VC.. 1103.. |
| ISO code toolholder | A20Q SVJCR/L11 |
| Minimum pre-drill Ø D_{min} | 24 mm |
| Head length L_1 | 38 mm |
| Insert size | 11 mm |
| Centre offset L_3 | 2 mm |
| Pack of insert screws | 269028 7 |
| Neck width L_4 | 11 mm |
| Overall length L | 180 mm |
| Clamping height L_2 | 19 mm |
| Setting angle κ | 142 degrees |
| Shank Ø D_s | 20 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 3×D |
| Through-coolant | yes |
| Application | Internal longitudinal turning |

| | |
|-----------------|------------|
| Type of product | Boring bar |
|-----------------|------------|

Accessories

| | |
|--------------------------------------------------------------------------------------|------------|
| Set of insert screws Type 7 | 269028 7 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |