

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	261331 16/11
GTIN	4045197653987
Item class	21T

Technical description

Pack of insert screws	269028 7
Insert size	11 mm
ISO code toolholder	AH16M SVJCR/L11
Centre offset L_3	4.6 mm
Neck width L_4	11.6 mm
suitable indexable insert	VC.. 1103..
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Head length L_1	30 mm
Overall length L	150 mm
Clamping height L_2	15 mm
Setting angle κ	142 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500