

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	261345 16/11
GTIN	4045197656179
Item class	21T

Technical description

Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	21 mm
Head length L_1	16.5 mm
ISO code toolholder	A16Q SVQCR/L11
Centre offset L_3	11 mm
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Overall length L	180 mm
Clamping height L_2	15.5 mm
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500