

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	261339 20/11
GTIN	4045197654113
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	24 mm
Head length L_1	38 mm
ISO code toolholder	A20Q SVJCR/L11
Neck width L_4	11 mm
Insert size	11 mm
Centre offset L_3	2 mm
Pack of insert screws	269028 7
suitable indexable insert	VC.. 1103..
Overall length L	180 mm
Clamping height L_2	19 mm
Setting angle κ	142 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500