

**Garant**
**Boring bar steel, left-hand, Shank  $\varnothing$  / insert size: 20/11 mm**


## Order data

Order number	261345 20/11
GTIN	4045197656186
Item class	21T

## Technical description

ISO code toolholder	A20R SVQCR/L11
Head length $L_1$	26.1 mm
Centre offset $L_3$	13 mm
Insert size	11 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	24 mm
suitable indexable insert	VC.. 1103..
Overall length L	200 mm
Clamping height $L_2$	19 mm
Setting angle $\kappa$	107.5 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500