

LOCTITE**Instant adhesive, 20 g, Manufacturer ID: 480**

Order data

Order number	083352 480
GTIN	4100630166131
Item class	04L

Description

Version:

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity.

Application:

Black high-impact instant adhesive for bonding metal to metal and **metal to rubber**. Best resistance to shear and impact stresses, and to moisture.

Note:

Not available in all countries. Express delivery not possible.

Technical description

Manufacturer's designation	LOCTITE 480
Labelling of hazardous substances	GHS07: Exclamation mark
Touch dry after	60 - 120 s
Tensile shear strength	22 - 30 N/mm ²
Dynamic viscosity	100 - 200 mPas

Storage temperature	2 - 8 °C
Density	1.05 g/cm ³
Working life after date of manufacture	17 mo
Operating temperature range	-40 - 100 °C
Characteristics	moisture-resistant
Characteristics	shock-resistant
Characteristics	impact-resistant
Suitable for material	Metal
Suitable for material	Plastic
Suitable for material	Glass
Suitable for material	Elastomer
Shape	liquid
Colour	black
Chemical basis	Ethyl cyanoacrylate
Capacity	20 ml
Maximum gap size	0.15 mm
Product name attribute	20 g
Type of product	Instant adhesive