

**Garant**
**Boring bar steel, left-hand, Shank Ø / insert size: 25/16mm**


## Order data

Order number	261345 25/16
GTIN	4045197654144
Item class	21T

## Technical description

Insert size	16 mm
Head length L <sub>1</sub>	43 mm
ISO code toolholder	A25R SVQCR/L16
Centre offset L <sub>3</sub>	17 mm
Pack of insert screws	269028 8
Minimum pre-drill Ø D <sub>min</sub>	31.5 mm
suitable indexable insert	VC.. 1604..
Overall length L	200 mm
Clamping height L <sub>2</sub>	23 mm
Setting angle κ	107.5 degrees
Shank Ø D <sub>s</sub>	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 8	269028 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500