

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	261349 20/11
GTIN	4045197654175
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	25 mm
Centre offset L_3	13 mm
Pack of insert screws	269028 7
Head length L_1	20.5 mm
suitable indexable insert	VC.. 1103..
Insert size	11 mm
ISO code toolholder	A20R SVUCR/L11
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500