

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 40/16mm

Order data

Order number	261345 40/16
GTIN	4045197656209
Item class	21T

Technical description

Shim screw	269013 2
Shim	269005 8
Pack of insert screws	269028 2
Insert size	16 mm
Head length L_1	40 mm
suitable indexable insert	VC.. 1604..
Minimum pre-drill $\varnothing D_{\min}$	49 mm
ISO code toolholder	A40T SVQCR/L16
Centre offset L_3	27 mm
Overall length L	300 mm
Clamping height L_2	39 mm
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 8	269005 8
Set of insert screws Type 2	269028 2
Shim screw Type 2	269013 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500