

**Garant**
**Boring bar steel, left-hand, Shank  $\varnothing$  / insert size: 32/16mm**

**Order data**

Order number	261349 32/16
GTIN	4045197656254
Item class	21T

**Technical description**

suitable indexable insert	VC.. 1604..
Shim screw	269013 2
Centre offset $L_3$	22 mm
ISO code toolholder	A32S SVUCR/L16
Head length $L_1$	33.5 mm
Insert size	16 mm
Pack of insert screws	269028 2
Shim	269005 8
Minimum pre-drill $\varnothing D_{\min}$	40 mm
Overall length L	250 mm
Clamping height $L_2$	31 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	32 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500