

Garant
Full profile insert 55°, external, right-hand, HB7125, TPI: 11


Order data

Order number	270803 11
GTIN	4045197463111
Item class	21J

Technical description

Number of turns/inch	11
Tool material	Carbide
Internal/external application	external
Application type	right-hand
Indexable insert profile	Full profile
Grade	HB7125
Thread type	BSW
Thread type	BSP-LH
Thread type	BSP
Thread type	BSW-LH
Thread type	G
Thread type	G-LH

Flank angle	55 degrees
Thickness	3.6 mm
Insert size L	16 mm
Type of product	Indexable insert for thread turning

User data

	Suitability	V_c	ISO code
INOX < 900 N/mm ²	suitable	120 m/min	M
INOX > 900 N/mm ²	suitable	120 m/min	M
Ti > 850 N/mm ²	suitable	60 m/min	S
continuous	suitable		
irregular	suitable		
interrupted	suitable		
wet maximum	suitable		