

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 20/11 mm

Order data

Order number	261344 20/11
GTIN	4045197656148
Item class	21T

Technical description

Insert size	11 mm
suitable indexable insert	VC.. 1103..
ISO code toolholder	A20R SVQCR/L11
Minimum pre-drill Ø D_{min}	24 mm
Head length L_1	26.1 mm
Centre offset L_3	13 mm
Pack of insert screws	269028 7
Overall length L	200 mm
Clamping height L_2	19 mm
Setting angle κ	107.5 degrees
Shank Ø D_s	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500