

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 25/16mm

Order data

Order number	261344 25/16
GTIN	4045197654137
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	31.5 mm
ISO code toolholder	A25R SVQCR/L16
suitable indexable insert	VC.. 1604..
Head length L_1	43 mm
Insert size	16 mm
Centre offset L_3	17 mm
Pack of insert screws	269028 8
Overall length L	200 mm
Clamping height L_2	23 mm
Setting angle κ	107.5 degrees
Shank Ø D_s	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 8	269028 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500