

**Garant**
**Boring bar steel, right-hand, Shank Ø / insert size: 20/11 mm**

**Order data**

Order number	261348 20/11
GTIN	4045197654151
Item class	21T

**Technical description**

Pack of insert screws	269028 7
ISO code toolholder	A20R SVUCR/L11
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Head length $L_1$	20.5 mm
suitable indexable insert	VC.. 1103..
Centre offset $L_3$	13 mm
Overall length $L$	200 mm
Clamping height $L_2$	18 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500