

Garant
Whistle Notch arbor Form ADB, SK 50 short, Clamping range \varnothing D1: 14mm

Order data

Order number	300450 14
GTIN	4045197284556
Item class	31A

Description
Version:

With back stop screw. Shanks hard turned (smooth cutting action!). With RFID/Balluffchip bore.

Advantage:

The tool is firmly clamped at the side with the clamping screw and supported at the back with the back stop screw. Clamping free of play, giving low vibration running.

Application:

For clamping tools with parallel shank **and whistle notch shanks** (2°) to DIN 1835 E and DIN 6535 HE.

- **The loss of length due to regrinding of the drill front can be corrected by axial length adjustment in the toolholder.**

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Spare clamping screw No. 30 9900	12
Overhang dimension A	63 mm
Clamping \varnothing D ₁	14 mm
External \varnothing D	44 mm
Adapter	SK 50 short
Standard	DIN 6359

Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull studForm B suitable for steep tapers 50	308640 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull studForm A suitable for steep tapers 50	308600 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull studsealed, form B suitable for steep tapers 50	308650 50

Spare clamping screw for chucks with clamping \varnothing D1 12 mm

309900 12