

LOCTITE.**Instant adhesive, 20 g, Manufacturer ID: 496**

Order data

Order number	083352 496
GTIN	4100630496160
Item class	04L

Description

Version:

Universally applicable for bonding dissimilar materials. Quick curing and clean, nearly invisible joints. Hardens by atmospheric humidity.

Application:

Universal instant adhesive for nearly all materials. Very suitable for **metals**. In comparison to size 401 slightly higher strength but less temperature stability.

Note:

Not available in all countries. Express delivery not possible.

Technical description

Tensile shear strength	20 - 30 N/mm ²
Touch dry after	20 - 40 s
Manufacturer's designation	LOCTITE 496
Labelling of hazardous substances	GHS07: Exclamation mark
Dynamic viscosity	125 mPas

Storage temperature	2 °C
hazardous goods class	9
Shape	liquid
Suitable for material	Plastic
Suitable for material	Metal
Suitable for material	Elastomer
Chemical basis	Methyl cyanoacrylate
Density	1.09 g/cm ³
Operating temperature range	-40 - 80 °C
Colour	transparent
Working life after date of manufacture	20 mo
Capacity	20 ml
Maximum gap size	15 mm
Product name attribute	20 g
Type of product	Instant adhesive