

**Garant**
**ER collet chuck Form ADB, SK 50 A = 200, for ER collet size: 25**

**Order data**

Order number	300625 25
GTIN	4045197284976
Item class	31A

**Description**
**Version:**

Taper ground internally and externally. With Balluff/RFID chip bore.

**GARANT –**

- **Balancing quality G2.5 / 25,000 rpm**
- **All shanks hard turned (for smooth running!).**
- **GARANT precision clamping nut, fine balanced (G 2.5 / 25,000 rpm) and coated, giving high clamping force and low wear.**
- **Through bored.**

**Application:**

For clamping tools with plain shank in collets to DIN 6499 - Form A and B.

**Supplied with:**

Clamping nut

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No.308820 – 308835, ER chuck key No. 309680 – 613300, ER collets No. 308901 – 309449, ER clamping nuts No. 309615 (for sealing rings), sealing rings No. 309625 – 309645 (for No. 309615).

Machining strategy: HSC

Clamping range: 1 - 16 mm

Overhang dimension A: 200 mm

External Ø D: 42 mm

Spare GARANT high-speed clamping nut No. 309610: 25

Spare HOLEX nut No. 309580: 25

## Technical description

Clamping range	1 - 16 mm
Spare GARANT high-speed clamping nut No. 309610	25
Overhang dimension A	200 mm
Spare HOLEX nut No. 309580	25
for ER collets	25
External $\varnothing$ D	42 mm
Clamping $\varnothing$ D <sub>1</sub>	1-16 mm
Adapter	SK 50 A = 200
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

## Accessories

ER collet with seal Nominal clamping $\varnothing$ d 9 mm	308959 9
ER collet with seal Nominal clamping $\varnothing$ d 6 mm	308946 6
ER collet set 15 pieces 2–16 mm	309240
ER collet Nominal clamping $\varnothing$ d 4 mm	308960 4
ET collet for thread tapping, with axial compensation Nominal clamping $\varnothing$ d 9 mm	309430 9
ER collet with seal and spray nozzles Nominal clamping $\varnothing$ d 16 mm	308962 16
ER clamping nut for HiRunER collet chucks for ER 25	309617 25
	308615 50

Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50

ER collet for machine taps with seal Nominal clamping Ø d 12 mm	309409 12
ER collet with seal Nominal clamping Ø d 12 mm	308959 12
ER collet Nominal clamping Ø d 9 mm	308960 9
ER clamping nut for ER 25	309580 25
ER chuck key for ER collet chuck 25	309680 25
ER collet Nominal clamping Ø d 11 mm	308941 11
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309447 4
Pull stud 45° sealed suitable for steep tapers 50	308760 50
ER collet Nominal clamping Ø d 4 mm	308941 4
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309411 6
ER collet with seal Nominal clamping Ø d 3 mm	308946 3
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309411 14
ER collet for machine taps with seal Nominal clamping Ø d 11 mm	309409 11
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309447 4,5
Torque insert for ER Mini nuts for ER collet chuck 25	309745 25
ER collet with seal and spray nozzles Nominal clamping Ø d 15 mm	308962 15
ER collet with seal and spray nozzles Nominal clamping Ø d 14 mm	308962 14
ER collet Nominal clamping Ø d 13 mm	308960 13
ER collet Nominal clamping Ø d 3 mm	308960 3
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309447 5
ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm	308962 5

ER collet with seal and spray nozzles Nominal clamping Ø d 6 mm	308962 6
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3 mm	309447 3
ER collet set 7 pieces 4–16 mm with seal	309022
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 14 mm	309413 14
ER collet with seal Nominal clamping Ø d 9 mm	308946 9
ER collet with seal Nominal clamping Ø d 8 mm	308946 8
ER collet Nominal clamping Ø d 11 mm	308960 11
ER collet Nominal clamping Ø d 9 mm	308941 9
ER collet with seal and spray nozzles Nominal clamping Ø d 11 mm	308962 11
ER collet with seal Nominal clamping Ø d 6 mm	308959 6
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309411 10
ER collet set 15 pieces 2–16 mm with seal	309244
Wrench for pull studs ISO 7388 suitable for ISO taper size 50	308830 50
ER collet for machine taps with seal Nominal clamping Ø d 11 mm	309411 11
ER collet with seal and spray nozzles Nominal clamping Ø d 8 mm	308962 8
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 9 mm	309413 9
ER collet with seal Nominal clamping Ø d 5 mm	308959 5
ER collet with seal Nominal clamping Ø d 3 mm	308959 3
Special pull stud with internal thread suitable for steep tapers 50	308740 50
ER collet with seal Nominal clamping Ø d 16 mm	308959 16
ER collet with seal and spray nozzles Nominal clamping Ø d 13 mm	308962 13
	309447 9

ET collet with radial compensation for tapping and reaming Nominal clamping  $\varnothing$  d 9 mm

ER collet with seal Nominal clamping $\varnothing$ d 12 mm	308946 12
Pull stud sealed, form A suitable for steep tapers 50	308610 50
ER collet for machine taps with seal Nominal clamping $\varnothing$ d 7 mm	309409 7
Pull stud 90° sealed suitable for steep tapers 50	308795 50
ER collet Nominal clamping $\varnothing$ d 5 mm	308960 5
ER collet with seal Nominal clamping $\varnothing$ d 5 mm	308946 5
ET collet with radial compensation for tapping and reaming Nominal clamping $\varnothing$ d 6 mm	309447 6
Pull stud 60° sealed suitable for steep tapers 50	308785 50
ER collet Nominal clamping $\varnothing$ d 7 mm	308941 7
ER collet set 15 pieces 2–16 mm with seal and spray nozzles	309245
ER collet for machine taps with seal Nominal clamping $\varnothing$ d 10 mm	309409 10
ER collet Nominal clamping $\varnothing$ d 2 mm	308960 2
ER collet for machine taps with seal Nominal clamping $\varnothing$ d 12 mm	309411 12
ER collet for machine taps with seal Nominal clamping $\varnothing$ d 8 mm	309409 8
ER collet for machine taps with seal and spray nozzles Nominal clamping $\varnothing$ d 12 mm	309413 12
Pull stud sealed suitable for steep tapers 50	308660 50
ER collet Nominal clamping $\varnothing$ d 12 mm	308941 12
ER collet for machine taps with seal and spray nozzles Nominal clamping $\varnothing$ d 4,5 mm	309413 4,5
ER collet Nominal clamping $\varnothing$ d 14 mm	308941 14
ET collet with radial compensation for tapping and reaming Nominal clamping $\varnothing$ d 7 mm	309447 7
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50

ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309411 8
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 10 mm	309413 10
ER collet Nominal clamping Ø d 13 mm	308941 13
ER collet with seal Nominal clamping Ø d 15 mm	308959 15
Pull stud sealed, form B suitable for steep tapers 50	308650 50
ER collet with seal Nominal clamping Ø d 11 mm	308946 11
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 7 mm	309413 7
ER plain bearing clamping nut for ER 25	309612 25
ER collet Nominal clamping Ø d 8 mm	308960 8
ER collet Nominal clamping Ø d 3 mm	308941 3
ER collet with seal and spray nozzles Nominal clamping Ø d 12 mm	308962 12
ER collet Nominal clamping Ø d 14 mm	308960 14
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309409 6
ER collet with seal Nominal clamping Ø d 16 mm	308946 16
ER collet Nominal clamping Ø d 12 mm	308960 12
Pull stud 90° sealed suitable for steep tapers 50	308790 50
ER collet Nominal clamping Ø d 10 mm	308941 10
ER collet with seal Nominal clamping Ø d 4 mm	308959 4
ER collet with seal and spray nozzles Nominal clamping Ø d 3 mm	308962 3
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 8 mm	309447 8
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309409 16
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 6 mm	309413 6
ER collet Nominal clamping Ø d 2 mm	308941 2

Torque insert for Pull studs to SO 7388 suitable for ISO taper size 50	308812 50
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309411 4,5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 7 mm	309430 7
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 11 mm	309413 11
Special pull stud with no internal thread sealed suitable for steep tapers 50	308700 50
ER collet with seal Nominal clamping Ø d 14 mm	308946 14
Pull stud Form B suitable for steep tapers 50	308640 50
ER collet with seal Nominal clamping Ø d 8 mm	308959 8
ER collet with seal and spray nozzles Nominal clamping Ø d 10 mm	308962 10
ER collet Nominal clamping Ø d 2,5 mm	308941 2,5
ER collet Nominal clamping Ø d 15 mm	308941 15
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309411 9
ER collet Nominal clamping Ø d 16 mm	308941 16
ER collet Nominal clamping Ø d 15 mm	308960 15
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309430 4,5
ER collet with seal Nominal clamping Ø d 11 mm	308959 11
ER collet Nominal clamping Ø d 6 mm	308941 6
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309411 16
Pull stud Form A suitable for steep tapers 50	308600 50
ER collet with seal Nominal clamping Ø d 7 mm	308959 7
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm	309447 10
Pull stud sealed, form B suitable for steep tapers 50	308620 50
ER collet Nominal clamping Ø d 7 mm	308960 7

ER collet Nominal clamping Ø d 8 mm	308941 8
ER collet with seal and spray nozzles Nominal clamping Ø d 7 mm	308962 7
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 8 mm	309413 8
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309430 3,5
Pull stud 45° sealed suitable for steep tapers 50	308765 50
ER clamping nut High Speed for ER 25	309610 25
ER collet with seal Nominal clamping Ø d 15 mm	308946 15
ER collet with seal Nominal clamping Ø d 14 mm	308959 14
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309430 6
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309409 4,5
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 50	308810 50
ER collet with seal Nominal clamping Ø d 10 mm	308959 10
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3,5 mm	309447 3,5
ER collet Nominal clamping Ø d 10 mm	308960 10
ER collet Nominal clamping Ø d 6 mm	308960 6
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309430 2,8
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50	308605 50
ER collet with seal Nominal clamping Ø d 10 mm	308946 10
ER collet with seal and spray nozzles Nominal clamping Ø d 4 mm	308962 4
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309411 7
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309409 14
ER collet with seal Nominal clamping Ø d 7 mm	308946 7



ER collet with seal Nominal clamping Ø d 13 mm	308959 13
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 10 mm	309430 10
ER collet Nominal clamping Ø d 16 mm	308960 16
ER collet with seal and spray nozzles Nominal clamping Ø d 9 mm	308962 9
ER collet Nominal clamping Ø d 5 mm	308941 5
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 8 mm	309430 8
ER collet with seal Nominal clamping Ø d 4 mm	308946 4
ER collet with seal Nominal clamping Ø d 13 mm	308946 13
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309409 9