

## Garant

### ER collet chuck Form ADB, SK 40 A = 160, for ER collet size: 40



#### Order data

Order number	300530 40
GTIN	4045197284792
Item class	31A

#### Description

##### Version:

Taper ground internally and externally. With Balluff/RFID chip bore.

##### GARANT –

- **Balancing quality G2.5 / 25,000 rpm**
- **All shanks hard turned (for smooth running!).**
- **GARANT precision clamping nut, fine balanced (G 2.5 / 25,000 rpm) and coated, giving high clamping force and low wear.**
- **Through bored.**

##### Application:

For clamping tools with plain shank in collets to DIN 6499 - Form A and B.

##### Supplied with:

Clamping nut

##### Optional extras:

Pull studs (PS) No. 308600 – 308806, PS pull stud wrenches No.308820 – 308835, ER chuck key No. 309680 – 613300, ER collets No. 308901 – 309449, ER clamping nuts No. 309615 (for sealing rings), sealing rings No. 309625 – 309645 (for No. 309615).

#### Technical description

Spare GARANT high-speed clamping nut No. 309610	40
Overhang dimension A	160 mm
for ER collets	40
Clamping range	3 - 26 mm

Spare HOLEX nut No. 309580	40
External Ø D	63 mm
Clamping Ø D <sub>1</sub>	3-26 mm
Adapter	SK 40 A = 160
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck

## Accessories

ER colletwith seal Nominal clamping Ø d 12 mm	308992 12
ER plain bearing clamping nut for ER 40	309612 40
ER collet Nominal clamping Ø d 6 mm	309040 6
ER collet for machine tapswith seal Nominal clamping Ø d 18 mm	309419 18
ER collet for machine tapswith seal Nominal clamping Ø d 8 mm	309419 8
ER collet for machine tapswith seal Nominal clamping Ø d 6 mm	309419 6
ER collet for machine tapswith seal Nominal clamping Ø d 22 mm	309419 22
ER collet Nominal clamping Ø d 14 mm	308990 14
ER chuck key for ER collet chuck 40	309680 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
ER collet Nominal clamping Ø d 8 mm	309040 8
ER collet Nominal clamping Ø d 21 mm	308990 21

ER collet Nominal clamping Ø d 20 mm	309040 20
Pull studForm A suitable for steep tapers 40	308600 40
ER collet set 23 pieces 4–26 mm	309028
ER collet Nominal clamping Ø d 12 mm	309040 12
Special pull stud with internal thread suitable for steep tapers 40	308740 40
ER collet Nominal clamping Ø d 21 mm	309040 21
ER collet Nominal clamping Ø d 10 mm	309040 10
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
ER collet Nominal clamping Ø d 5 mm	309040 5
ER collet Nominal clamping Ø d 15 mm	308990 15
ER collet Nominal clamping Ø d 26 mm	308990 26
Pull studsealed suitable for steep tapers 40	308635 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
ER collet Nominal clamping Ø d 23 mm	308990 23
ER collet Nominal clamping Ø d 17 mm	308990 17
ER colletwith seal Nominal clamping Ø d 25 mm	308992 25
ER collet Nominal clamping Ø d 15 mm	309040 15
ER collet Nominal clamping Ø d 18 mm	309040 18
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
ER collet Nominal clamping Ø d 22 mm	308990 22
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
ER collet Nominal clamping Ø d 17 mm	309040 17
ER collet Nominal clamping Ø d 19 mm	308990 19
ER collet for machine tapswith seal Nominal clamping Ø d 14 mm	309419 14
ER clamping nutHigh Speed for ER 40	309610 40

ER collet for machine tapswith seal Nominal clamping Ø d 9 mm	309419 9
Pull studForm B suitable for steep tapers 40	308640 40
ER colletwith seal Nominal clamping Ø d 10 mm	308992 10
ER collet for machine tapswith seal Nominal clamping Ø d 10 mm	309419 10
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 10 mm	309449 10
ER clamping nutfor HiRunER collet chucks for ER 40	309617 40
ER collet Nominal clamping Ø d 24 mm	308990 24
ER collet Nominal clamping Ø d 14 mm	309040 14
ER collet Nominal clamping Ø d 25 mm	309040 25
ER collet Nominal clamping Ø d 12 mm	308990 12
ER colletwith seal Nominal clamping Ø d 6 mm	308992 6
ER collet Nominal clamping Ø d 6 mm	308990 6
Pull stud 45°sealed suitable for steep tapers 40	308760 40
ER colletwith seal Nominal clamping Ø d 22 mm	308992 22
ER collet for machine tapswith seal Nominal clamping Ø d 20 mm	309419 20
ER collet Nominal clamping Ø d 4 mm	309040 4
ER collet Nominal clamping Ø d 20 mm	308990 20
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
ER colletwith seal Nominal clamping Ø d 14 mm	308992 14
ER collet set 15 pieces 2–16 mm	309240
ER collet for machine tapswith seal Nominal clamping Ø d 25 mm	309419 25
Pull stud 60°sealed suitable for steep tapers 40	308785 40
ER collet Nominal clamping Ø d 5 mm	308990 5
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
ER collet Nominal clamping Ø d 11 mm	309040 11

ER collet Nominal clamping Ø d 7 mm	309040 7
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309419 16
ER collet Nominal clamping Ø d 4 mm	308990 4
Pull stud sealed, form A suitable for steep tapers 40	308610 40
ER collet set 23 pieces 4–26 mm	309320
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
ER collet Nominal clamping Ø d 26 mm	309040 26
ER collet Nominal clamping Ø d 13 mm	308990 13
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
ER collet with seal Nominal clamping Ø d 18 mm	308992 18
ER collet with seal Nominal clamping Ø d 8 mm	308992 8
ER collet with seal Nominal clamping Ø d 20 mm	308992 20
ER collet for machine taps with seal Nominal clamping Ø d 11 mm	309419 11
Pull stud sealed suitable for steep tapers 40	308660 40
ER collet Nominal clamping Ø d 25 mm	308990 25
Pull stud 90° sealed suitable for steep tapers 40	308795 40
ER collet Nominal clamping Ø d 7 mm	308990 7
ER collet with seal Nominal clamping Ø d 16 mm	308992 16
ER collet Nominal clamping Ø d 8 mm	308990 8
ER collet Nominal clamping Ø d 10 mm	308990 10
ER collet Nominal clamping Ø d 24 mm	309040 24
ER collet Nominal clamping Ø d 9 mm	309040 9
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309419 7
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
ER collet Nominal clamping Ø d 13 mm	309040 13

ER collet Nominal clamping Ø d 9 mm	308990 9
ER collet Nominal clamping Ø d 19 mm	309040 19
ER collet Nominal clamping Ø d 23 mm	309040 23
ER clamping nut for ER 40	309580 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
ER collet Nominal clamping Ø d 22 mm	309040 22
ER collet Nominal clamping Ø d 16 mm	308990 16
ER collet Nominal clamping Ø d 16 mm	309040 16
ER collet Nominal clamping Ø d 11 mm	308990 11
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
ER collet Nominal clamping Ø d 18 mm	308990 18
ER collet for machine tapwith seal Nominal clamping Ø d 12 mm	309419 12