

Garant
ER collet chuck mini / slim Form ADB, SK 40 A = 100, for ER collet size: 11


Order data

Order number	300650 11
GTIN	4045197287762
Item class	31A

Description

Version:

Clamping nut fine balanced **for HSC**. ER11 through bored. Shanks hard turned (smooth cutting action!).

· **With Balluffchip bore as standard.**

Application:

For clamping tools with plain shank to DIN 6499.

Supplied with:

High speed ER mini nut No. 309650.

Optional extras:

ER collets No. 308881 – 309434, ER lock wrench No. 309740.

Pull studs (PS) No. 308600 – 308806. PS chuck key No. 308820; 308830.

Technical description

for ER collets	11 mm
Clamping range	0.5 - 7 mm
Overhang dimension A	100 mm
Suitable chuck key No. 309740	11
External \varnothing D	16 mm
Usable length L_N	70 mm
Clamping \varnothing D_1	1-7 mm

Adapter	SK 40 A = 100
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Collet chuck

Accessories

Pull stud 45°sealed suitable for steep tapers 40	308760 40
ER colletwith seal Nominal clamping Ø d 5 mm	308882 5
ER collet set 15 pieces 2–16 mm	309240
ER collet Nominal clamping Ø d 1 mm	308881 1
ER collet Nominal clamping Ø d 1 mm	308918 1
ER collet Nominal clamping Ø d 6 mm	308881 6
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
ER collet Nominal clamping Ø d 5 mm	308881 5
Wrench for ER Mini nuts for ER collet chuck 11	309740 11
ER colletwith seal Nominal clamping Ø d 6 mm	308882 6
ER collet set 7 pieces 1–7 mm	309155
ER collet Nominal clamping Ø d 6 mm	308918 6
Pull studsealed suitable for steep tapers 40	308660 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
ER collet Nominal clamping Ø d 5,5 mm	308881 5,5
ER collet Nominal clamping Ø d 2 mm	308918 2

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
ER collet set 13 pieces 1–7 mm	309010
ER collet Nominal clamping Ø d 4,5 mm	308881 4,5
Pull stud 90°sealed suitable for steep tapers 40	308795 40
ER collet Nominal clamping Ø d 4 mm	308918 4
ER collet Nominal clamping Ø d 7 mm	308881 7
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studForm B suitable for steep tapers 40	308640 40
ER collet Nominal clamping Ø d 3 mm	308881 3
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
ER chuck key for ER collet chuck 40	309680 40
ER collet Nominal clamping Ø d 1,5 mm	308881 1,5
Pull studsealed, form A suitable for steep tapers 40	308610 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
ER chuck key1/2 inch socket for ER collet chuck 40	309700 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
ER collet Nominal clamping Ø d 5 mm	308918 5
ER collet Nominal clamping Ø d 3 mm	308918 3
Special pull stud with internal thread suitable for steep tapers 40	308740 40
ER collet Nominal clamping Ø d 2 mm	308881 2

ER collet Nominal clamping Ø d 6,5 mm	308881 6,5
ER collet Nominal clamping Ø d 7 mm	308918 7
Special pull stud with no internal threadsealed suitable for steep tapers 40	308720 40
ER collet Nominal clamping Ø d 2,5 mm	308881 2,5
ER colletwith seal Nominal clamping Ø d 4 mm	308882 4
ER collet Nominal clamping Ø d 4 mm	308881 4
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
ER colletwith seal Nominal clamping Ø d 3 mm	308882 3
ER collet Nominal clamping Ø d 3,5 mm	308881 3,5
ER collet for machine taps Nominal clamping Ø d 4,5 mm	309399 4,5
ER collet for machine taps Nominal clamping Ø d 2,5 mm	309399 2,5
ER collet for machine taps Nominal clamping Ø d 3,5 mm	309399 3,5
ER collet for machine taps Nominal clamping Ø d 2,8 mm	309399 2,8
ER collet for machine taps Nominal clamping Ø d 6 mm	309399 6
ER collet for machine taps Nominal clamping Ø d 4 mm	309399 4