

Offset screwdriving attachment, Type: OSD2



Order data

Order number	073920 OSD2
GTIN	4002395369799
Item class	07A

Description

Version:

Suitable for all commercially available screwdrivers and drilling machines. Gear of high-quality steel. Width across corners 30 mm. Bearing shell with retaining flange for torque support can be turned 360° to any angle. Mounting magnetised, corresponds to 1/4 inch bit hexagon. Offset screwdriving / drill attachment is the ideal solution for all screw fastenings in restricted and inaccessible places.

1/4 inch magnetic hexagon socket, suitable for all standard bits 25 mm (C 6.3) and ball-lock bits (E 6.3).

Technical description

maximum torque	40 Nm
Type	OSD2
Type of product	Screwdriver attachment