



CENTRO P ER collet holder cylindrical, for ER collet size: 16



Order data

Order number	300682 16
GTIN	2050001705686
Item class	33F

Description

Version:

Fahrion CENTRO P cylindrical holder **without clamping nuts**.
Through hole for internal cooling provided.

Application:

For extending the reach of side lock arbors or collet chucks.

Optional extras:

Clamping wrenches No. 309754; 309756.

ER collets No. 309365 – 309372, ER mini nut CP No. 309655; 309665.

Note:

Not suitable for shrink processes.

Technical description

L ₂	33 mm
Shank length L ₁	117 mm
for ER collets	16
Shank Ø d	16 mm
Clamping range	0.5 - 10 mm
External Ø D	22 mm
Series	Centro P
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm

Machining strategy	HSC
Type of product	Collet chuck

Accessories

ER clamping nut CENTRO PStandard Type CP for ER 11M	309655 11M
ER collet HP Nominal clamping Ø d 2 mm	309365 2
ER clamping nut CENTRO Pfor HP sealing rings Type CP for ER 25DI	309665 25DI
ER collet HP Nominal clamping Ø d 9 mm	309370 9
ER clamping nut CENTRO Pfor HP sealing rings Type CP for ER 32DI	309665 32DI
ER clamping nut CENTRO PStandard Type CP for ER 16C	309655 16C
ER collet HPwith seal Nominal clamping Ø d 5 mm	309369 5
ER clamping nut CENTRO PStandard Type CP for ER 16MS	309655 16MS
ER collet HPwith seal Nominal clamping Ø d 5 mm	309371 5
ER collet HP Nominal clamping Ø d 1 mm	309370 1
ER clamping nut CENTRO Pfor HP sealing rings Type CP for ER 16DI	309665 16DI
ER clamping nut CENTRO PStandard Type CP for ER 40	309655 40
ER clamping nut CENTRO PStandard Type CP for ER 25	309655 25
ER clamping nut CENTRO PStandard Type CP for ER 8M	309655 8M
ER collet HP Nominal clamping Ø d 7 mm	309370 7
ER collet HP Nominal clamping Ø d 3 mm	309370 3
ER collet HPwith seal Nominal clamping Ø d 7 mm	309371 7
ER collet HP Nominal clamping Ø d 3 mm	309368 3
ER collet HP Nominal clamping Ø d 2 mm	309370 2
ER collet HP Nominal clamping Ø d 6 mm	309368 6
ER clamping nut CENTRO Pfor HP sealing rings Type CP for ER 40DI	309665 40DI

ER collet HP Nominal clamping Ø d 5 mm	309368 5
ER collet HP Nominal clamping Ø d 3 mm	309365 3
ER collet HP Nominal clamping Ø d 1 mm	309365 1
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 6 mm	309372 6
ER collet HP Nominal clamping Ø d 10 mm	309370 10
ER clamping nut CENTRO PStandard Type CP for ER 32	309655 32
ER collet HPwith seal Nominal clamping Ø d 6 mm	309371 6
ER collet HP Nominal clamping Ø d 6 mm	309370 6
ER collet HPwith seal Nominal clamping Ø d 6 mm	309369 6
ER collet HPwith seal Nominal clamping Ø d 4 mm	309371 4
ER collet HP Nominal clamping Ø d 2 mm	309368 2
ER collet HP Nominal clamping Ø d 1 mm	309368 1
ER collet HP Nominal clamping Ø d 4 mm	309365 4
ER collet HP Nominal clamping Ø d 4 mm	309370 4
ER collet HPwith seal Nominal clamping Ø d 3 mm	309369 3
ER collet HP Nominal clamping Ø d 5 mm	309370 5
ER collet HPwith seal Nominal clamping Ø d 8 mm	309371 8
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 4 mm	309372 4
ER collet HPwith seal and spray nozzles Nominal clamping Ø d 8 mm	309372 8
ER collet HP Nominal clamping Ø d 7 mm	309368 7
ER collet HP Nominal clamping Ø d 5 mm	309365 5
ER collet HPwith seal Nominal clamping Ø d 9 mm	309371 9
ER clamping nut CENTRO PStandard Type CP for ER 16	309655 16
ER collet HPwith seal Nominal clamping Ø d 4 mm	309369 4
ER collet HPwith seal Nominal clamping Ø d 10 mm	309371 10
ER collet HPwith seal Nominal clamping Ø d 3 mm	309371 3
ER collet HP Nominal clamping Ø d 4 mm	309368 4

ER collet HP Nominal clamping \varnothing d 8 mm	309370 8
ER clamping nut CENTRO Pfor HP sealing rings Type CP for ER 16CDI	309665 16CDI
ER clamping nut CENTRO Pfor HP sealing rings Type CP for ER 16MSDI	309665 16MSDI