

**Garant**
**ER mini collet holder cylindrical, for ER collet size: 11**

**Order data**

Order number	300685 11
GTIN	4045197291806
Item class	31A

**Description**
**Version:**

Cylindrical holder with Weldon shank and ER nut.  
Through hole for internal cooling provided.

**Application:**

For extending the reach of side lock arbors or collet chucks.

**Optional extras:**

Clamping wrenches No. 309680 – 309740.  
ER collets No. 308878 – 309434, Spare ER nuts No. 309580; 309650.

**Note:**

Not suitable for shrink processes.

**Technical description**

L <sub>2</sub>	19 mm
Clamping range	0.5 - 7 mm
Shank Ø d	16 mm
Shank length L <sub>1</sub>	150 mm
for ER collets	11 mm
External Ø D	16 mm
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm

Machining strategy	HSC
Type of product	Collet chuck

## Accessories

ER collet Nominal clamping Ø d 1,5 mm	308881 1,5
ER collet HPwith seal Nominal clamping Ø d 4 mm	309369 4
ER collet HP Nominal clamping Ø d 3 mm	309368 3
ER collet Nominal clamping Ø d 1 mm	308881 1
ER colletwith seal Nominal clamping Ø d 6 mm	308882 6
ER collet Nominal clamping Ø d 3 mm	308881 3
ER collet HP Nominal clamping Ø d 7 mm	309368 7
ER collet Nominal clamping Ø d 4 mm	308881 4
ER collet HPwith seal Nominal clamping Ø d 3 mm	309369 3
ER collet set 13 pieces 1–7 mm	309010
ER collet Nominal clamping Ø d 2 mm	308918 2
ER collet HP Nominal clamping Ø d 5 mm	309368 5
ER colletwith seal Nominal clamping Ø d 4 mm	308882 4
ER collet Nominal clamping Ø d 4 mm	308918 4
ER collet HPwith seal Nominal clamping Ø d 5 mm	309369 5
ER collet HP Nominal clamping Ø d 6 mm	309368 6
ER collet Nominal clamping Ø d 3,5 mm	308881 3,5
ER collet Nominal clamping Ø d 5 mm	308918 5
ER collet HP Nominal clamping Ø d 2 mm	309368 2
ER collet Nominal clamping Ø d 2 mm	308881 2
ER collet HPwith seal Nominal clamping Ø d 6 mm	309369 6
ER collet Nominal clamping Ø d 7 mm	308918 7
ER collet Nominal clamping Ø d 1 mm	308918 1
ER collet set 7 pieces 1–7 mm	309155

ER collet Nominal clamping Ø d 3 mm	308918 3
ER collet Nominal clamping Ø d 5,5 mm	308881 5,5
ER collet Nominal clamping Ø d 6 mm	308918 6
ER colletwith seal Nominal clamping Ø d 3 mm	308882 3
ER collet Nominal clamping Ø d 4,5 mm	308881 4,5
ER collet Nominal clamping Ø d 7 mm	308881 7
ER collet HP Nominal clamping Ø d 4 mm	309368 4
ER collet HP Nominal clamping Ø d 1 mm	309368 1
ER collet Nominal clamping Ø d 6,5 mm	308881 6,5
ER collet Nominal clamping Ø d 6 mm	308881 6
ER colletwith seal Nominal clamping Ø d 5 mm	308882 5
ER collet Nominal clamping Ø d 5 mm	308881 5
ER collet Nominal clamping Ø d 2,5 mm	308881 2,5
ER Mini clamping nut for ER 11	309650 11
ER collet for machine taps Nominal clamping Ø d 6 mm	309399 6
ER collet for machine taps Nominal clamping Ø d 4,5 mm	309399 4,5
ER collet for machine taps Nominal clamping Ø d 2,5 mm	309399 2,5
ER collet for machine taps Nominal clamping Ø d 3,5 mm	309399 3,5
ER collet for machine taps Nominal clamping Ø d 2,8 mm	309399 2,8
ER collet for machine taps Nominal clamping Ø d 4 mm	309399 4