

**Garant**

**Boring bar with fixed 1.5° inclination angle, left-hand, Overhang / insert size L: 25/11 mm**

**Order data**

Order number	272142 25/11
GTIN	4045197429599
Item class	21W

**Description**

**Version:**  
**With fixed inclination angle.**  
**With internal cooling.**

**Technical description**

Insert screw	279810 4
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Centre offset $L_3$	7.3 mm
Overall length L	180 mm
Through-coolant	yes
Shank $\varnothing D_s$	20 mm
Inclination angle	1.5 degrees
Application type	left-hand
Type of product	Boring bar

**Accessories**

Insert screw Type 4	279810 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500