

**Garant**

**Boring bar with fixed 2.5° inclination angle, right-hand, Overhang / insert size L: 32/16mm**

**Order data**

Order number	272101 32/16
GTIN	4045197430595
Item class	21W

**Description****Version:**

**With fixed inclination angle. With internal cooling.**

**Application:**

For coarse threads M20×2.5; M22×2.5 and M24×3.

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	17 mm
Insert screw	279810 5
Centre offset $L_3$	10.3 mm
Insert size	16 mm
Overall length L	180 mm
Through-coolant	yes
Shank $\varnothing D_s$	20 mm
Inclination angle	2.5 degrees
Application type	right-hand
Type of product	Boring bar

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10
Insert screw Type 7	279810 7
Insert screw Type 5	279810 5
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200