

**Garant**
**Threading insert set size 16, HB7010, Type: EL**

**Order data**

Order number	271900 EL
GTIN	4045197371492
Item class	21J

**Description**
**Content:**

Full profile, metric 60°: No. 270720 size 1; 1.25; 1.5; 2; 2.5; 3

Partial profile, metric 60°: No. 270745 size 0.5-1.5; 1.75-3

Full profile, BSW 55°: No. 270805 size 14; 11

**Technical description**

Machining direction	left-hand
Tool material	Carbide
Thread type	M
Thread type	M-LH
Thread type	MF
Thread type	G
Thread type	BSW
Thread type	MF-LH
Thread type	G-LH
Thread type	BSW-LH
Grade	HB7010

Type of product

Indexable insert for thread turning

## Accessories

Full profile insert 60°, internal, left-hand Pitch 1,75 mm	270776 1,75
Full profile insert 60°, external, left-hand Pitch 2 mm	270720 2
Full profile insert 60°, external, left-hand Pitch 1,5 mm	270720 1,5
Partial profile insert 60°, internal, left-hand Pitch 1,75-3 mm	270797 1,75-3
Full profile insert 60°, external, left-hand Pitch 2,5 mm	270720 2,5
Full profile insert 55°, internal, left-hand TPI 11	270834 11
Full profile insert 60°, external, left-hand Pitch 1,25 mm	270720 1,25
Full profile insert 60°, internal, left-hand Pitch 3 mm	270776 3
Full profile insert 60°, external, left-hand Pitch 1 mm	270720 1
Full profile insert 55°, internal, left-hand TPI 14	270834 14
Full profile insert 60°, internal, left-hand Pitch 1,5 mm	270776 1,5
Full profile insert 55°, external, left-hand TPI 11	270805 11
Partial profile insert 60°, internal, left-hand Pitch 0,5-1,5 mm	270797 0,5-1,5
Full profile insert 60°, internal, left-hand Pitch 2,5 mm	270776 2,5
Full profile insert 60°, external, left-hand Pitch 3 mm	270720 3
Partial profile insert 60°, external, left-hand Pitch 0,5-1,5 mm	270745 0,5-1,5
Full profile insert 60°, internal, left-hand Pitch 1 mm	270776 1
Full profile insert 55°, external, left-hand TPI 14	270805 14
Full profile insert 60°, internal, left-hand Pitch 2 mm	270776 2
Partial profile insert 60°, external, left-hand Pitch 1,75-3 mm	270745 1,75-3