

Garant

Boring bar with fixed 1.5° inclination angle, right-hand, Overhang / insert size L: 60/11 mm

**Order data**

Order number	272111 60/11
GTIN	4045197584175
Item class	21W

Description

Version:
With fixed inclination angle.
With internal cooling.

Technical description

Insert size	11 mm
Insert screw	279810 4
Centre offset L ₃	7.3 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Overall length L	100 mm
Through-coolant	yes
Shank $\varnothing D_s$	10 mm
Inclination angle	1.5 degrees
Application type	right-hand
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Insert screw Type 4	279810 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500