

**Garant****Boring bar, right-hand, Overhang / insert size L: 60/16mm****Order data**

Order number	272171 60/16
GTIN	4045197430717
Item class	21W

**Description**

**Supplied with:**  
**With shim 1.5°.**

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	29 mm
Insert size	16 mm
Insert screw	279810 2
Centre offset $L_3$	16.3 mm
Overall length L	250 mm
Through-coolant	yes
Shim 1.5°	272620 1.5
Shim screw	279824 1
Shank $\varnothing D_s$	32 mm
Neck width $L_4$	25 mm
Application type	right-hand
Type of product	Boring bar

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10
Insert screw Type 2	279810 2
Shim screw Type 1	279824 1
Clamping screw	272500
Shim for boring bars Inclination angle 1,5 °	272620 1,5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500