

**Garant**

**Boring bar with fixed 1.5° inclination angle, right-hand, Overhang / insert size L: 40/16mm**

**Order data**

Order number	272111 40/16
GTIN	4045197430625
Item class	21W

**Description**

**Version:**  
**With fixed inclination angle.**  
**With internal cooling.**

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	20 mm
Centre offset $L_3$	11.5 mm
Insert screw	279810 5
Insert size	16 mm
Overall length L	180 mm
Through-coolant	yes
Shank $\varnothing D_s$	20 mm
Inclination angle	1.5 degrees
Application type	right-hand
Type of product	Boring bar

**Accessories**

Insert screw Type 5	279810 5
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200