

Garant
Combination face mill adapter Form ADB, SK 40 A = 100, Spigot Ø d1: 40mm

Order data

Order number	300845 40
GTIN	4045197285188
Item class	31A

Description
Version:

Taper shank, spigot, and all contact surfaces are ground at the collar. With Balluff/RFID chip bore.
GARANT –All shanks hard turned (for smooth cutting action!).

Application:

- **With drive key for mills with longitudinal keyway, e. g. DIN 841.**
- **With face mill drive ring for face mills with cross keyway, DIN 1880 and cutter heads to DIN 1830.**

Supplied with:

Drive key, face mill drive ring, and lock screw.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840.

Note:

Internal cooling available only with suitable tightening screw No. 309861.

Technical description

Suitable toggle spanner No. 309840	40
Spare drive ring No. 309870	40
Milling mandrel length L ₄	41 mm
Overhang dimension A	100 mm
Spigot Ø d ₁	40 mm

Milling mandrel length L ₃ with drive ring	27 mm
External Ø D	70 mm
Spare milling cutter lock screw No. 309860 / 309861	40
Clamping Ø D ₁	40 mm
Adapter	SK 40 A = 100
Standard	DIN 6358
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Type of product	Milling cutter spigot

Accessories

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40

Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Pull stud sealed, form A suitable for steep tapers 40	308610 40
Milling cutter lock screw for mandrel Ø 40 mm	309860 40
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud Form A suitable for steep tapers 40	308600 40
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud sealed, form B suitable for steep tapers 40	308620 40
Toggle spanner for mandrel Ø 40 mm	309840 40
Pull stud sealed suitable for steep tapers 40	308660 40
Face mill drive ring for mandrel Ø 40 mm	309870 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Pull stud sealed suitable for steep tapers 40	308635 40
Pull stud sealed, form B suitable for steep tapers 40	308650 40