

Garant
Threading insert set size 16, HB7010, Type: ER

Order data

Order number	271900 ER
GTIN	4045197370969
Item class	21J

Description
Content:

Full profile, metric 60°: No. 270700 size 1; 1.25; 1.5; 2; 2.5; 3
 Partial profile, metric 60°: No. 270740 size 0.5-1.5; 1.75-3
 Full profile, BSW 55°: No. 270800 size 14; 11

Technical description

Machining direction	right-hand
Tool material	Carbide
Thread type	M
Thread type	M-LH
Thread type	MF
Thread type	G
Thread type	BSW
Thread type	MF-LH
Thread type	G-LH
Thread type	BSW-LH
Grade	HB7010

Type of product

Indexable insert for thread turning

Accessories

Partial profile insert 60°, external, right-hand Pitch 0,5-1,5 mm	270740 0,5-1,5
Partial profile insert 60°, external, right-hand Pitch 1,75-3 mm	270740 1,75-3
Full profile insert 60°, external, right-hand Pitch 3 mm	270700 3
Full profile insert 60°, external, right-hand Pitch 1,25 mm	270700 1,25
Full profile insert 60°, external, right-hand Pitch 1 mm	270700 1
Full profile insert 60°, external, right-hand Pitch 1,5 mm	270700 1,5
Full profile insert 60°, external, right-hand Pitch 2,5 mm	270700 2,5
Full profile insert 60°, external, right-hand Pitch 2 mm	270700 2