

**LOCTITE****2-component adhesive, Manufacturer ID: 3430**

## Order data

Order number	083371 3430
GTIN	5010266253992
Item class	04L

## Description

**Version:**

**Tough resilient 2-component adhesive** for quick and easy jointing, makes a permanent joint. Cures at room temperature.

For permanent bonding between dissimilar materials such as wood, metals, hard plastics, and glass. High shear and peel strength. Quick-curing 5-minute epoxy is ideal for bonding transparent parts.

## Technical description

Tensile shear strength	22 N/mm <sup>2</sup>
Manufacturer's designation	LOCTITE 3430
Dynamic viscosity	23000 mPas
Processing temperature	20 °C
Chemical basis	Epoxy resin
Characteristics	water-resistant
Characteristics	impact-resistant

Shape	liquid
Storage temperature	8 °C
Operating temperature range	-55 - 100 °C
Suitable for material	Glass
Suitable for material	wood
Suitable for material	Metal
Suitable for material	porous materials
Suitable for material	Stainless steel
Colour	transparent
Working life after date of manufacture	24 mo
Hardness according to Shore A	70
Processing time	240 s
Capacity	24 g
Tensile strength	36 N/mm <sup>2</sup>
Density	1.14 g/cm <sup>3</sup>
Functional strength to	15 min
Touch dry after	7 min
Maximum gap size	5 mm
Type of product	Two-component adhesive