

**WEKEM®**
**High-temperature silicone tube, 80 ml, Colour: RED**

**Order data**

Order number	083493 RED
GTIN	4260205360323
Item class	08G

**Description**
**Version:**

**Silicone cartridges** for gasketing, bonding, sealing, and compensation for tolerance and temperature differences.

**Application:**

Sealing engine casings, gearbox, valve and housing covers, sumps, oil pumps, water pumps, heating systems, industrial ovens and stoves, exhaust systems, air conditioning devices, battery boxes and floodlights.

**Technical description**

Manufacturer's designation	HT silicone
Colour	red
Kinematic viscosity	20.5 mm <sup>2</sup> /s
Suitable for material	Aluminium
Suitable for material	Stainless steel
Suitable for material	Stainless steel (INOX)

Suitable for material	Glass
Flashpoint	100 °C
Stretch capability	300 %
Working life after date of manufacture	12 mo
Functional strength to	1440 min
Chemical basis	Silicone
Touch dry after	5 min
Shape	paste
Disassembly	with normal tool
Characteristics	weatherproof
Characteristics	oil-resistant
Characteristics	resistant to grease
Characteristics	permanently elastic
Processing temperature	5 - 35 °C
Storage temperature	5 - 25 °C
Capacity	80 ml
Hardness according to Shore A	30
Density	1.08 g/cm <sup>3</sup>
Operating temperature range	-60 - 260 °C
Product name attribute	80 ml
Type of product	Sealing compound

## Accessories

Compressed-air cartridge gun	083507
Fully enclosed cartridge gun assortment,4 pieces Type	083502
Cartridge gun12:1 Type	083501
Cartridge gun	083500