

**HOLEX®**
**Milling head arbor Form A, SK 50 short, Spigot Ø d1: 32 mm**

**Order data**

Order number	301100 32
GTIN	4045197145819
Item class	32A

**Description**
**Version:**

- From clamping Ø 40 with 4 tapped holes for face mills to DIN 2079.
- Taper shank, spigot, and all contact surfaces ground at the collar.
- Short series.
- Increased collar contact surface.
- With Balluffchip bore.

**Supplied with:**

Lock screw

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840.

Overhang dimension A: 50 mm

External Ø D: 78 mm

 Milling mandrel length L<sub>4</sub>: 24 mm

Spare milling cutter lock screw 309860: 32

suitable special toggle spanner 309840: 32

**Technical description**

suitable special toggle spanner 309840	32
Spare milling cutter lock screw 309860	32
Overhang dimension A	50 mm
Spigot Ø d <sub>1</sub>	32 mm

Milling mandrel length L <sub>4</sub>	24 mm
External Ø D	78 mm
Adapter	SK 50 short
Norm	DIN 6357
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC

## Accessories

Pull stud stud sealed, form A suitable for steep tapers 50	308610 50
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50	308605 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Pull stud 45° sealed suitable for steep tapers 50	308760 50
Pull stud Form B suitable for steep tapers 50	308640 50
Pull stud sealed suitable for steep tapers 50	308660 50
Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 50 SK	308830 50
Milling cutter lock screw for mandrel Ø 50 mm	309860 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50
Torque insert for Pull studs to SO 7388 suitable for steep tapers 50 SK	308812 50
Milling cutter lock screw for mandrel Ø 32 mm	309860 32
Toggle spanner for mandrel Ø 32 mm	309840 32
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
Pull stud sealed, form B suitable for steep tapers 50	308620 50

Torque insert for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308810 50
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50	308615 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Pull stud sealed, form B suitable for steep tapers 50	308650 50
Pull stud Form A suitable for steep tapers 50	308600 50
Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308820 50
Toggle spanner for mandrel Ø 50 mm	309840 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Special pull stud with no internal thread sealed suitable for steep tapers 50	308700 50
Pull stud 45° sealed suitable for steep tapers 50	308765 50