


**DCMW 11T308, KBN35M, Type: MET**

**Order data**

Order number	265696 MET
GTIN	4960664544288
Item class	25H

**Description**
**Version:**

**MEGACOAT** coated CBN inserts. MultiEdge Tough; 2 cutting edges per insert, with special honing for optimisation of interrupted cutting.

**Technical description**

Feed f	0.1 - 0.2 mm/rev.
Cutting depth $a_p$	0.05 - 0.5 mm
Cutting conditions	slightly interrupted
Cutting speed $v_c$ main application	100 - 180 m/min
Corner radius	0.8 mm
Cutting edge version	MET
Grade	KBN35M
Finishing/roughing assignment	Finishing
Tool material	CBN

ISO code indexable insert	DCMW 11T308
Number of changes/inserts	2
Product name attribute	KBN35M
Type of product	Indexable insert for turning

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
irregular	suitable only under restricted conditions		
interrupted	suitable		
dry	suitable		