


**DCMW 11T304, KBN35M, Type: MET**

**Order data**

Order number	265690 MET
GTIN	4960664544271
Item class	25H

**Description**
**Version:**

MEGACOAT-coated CBN inserts. MultiEdge Tough; 2 cutting edges per insert, with special honing for optimisation of interrupted cutting.

Grade: KBN35M

Chip breaker: MET

Cutting depth  $a_p$ : 0.05 - 0.5 mm

Feed  $f$ : 0.1 - 0.2 mm/rev.

Cutting speed  $v_c$  main application: 100 - 180 m/min

**Technical description**

Cutting depth $a_p$	0.05 - 0.5 mm
Cutting conditions	slightly interrupted
Feed $f$	0.1 - 0.2 mm/rev.
Chip breaker	MET
Cutting speed $v_c$ main application	100 - 180 m/min
Corner radius	0.4 mm

Grade	KBN35M
Finishing/roughing assignment	Finishing
Tool material	CBN
ISO code indexable insert	DCMW 11T304
Number of changes/inserts	2
Product name attribute	KBN35M
Type of product	Indexable insert for turning