

**Battery / mains radio, Type: M18RC****Order data**

Order number	073960 M18RC
GTIN	4002395005420
Item class	03L

Description**Version:**

Sturdy site radio, splash-proof (IP54) for mains and battery operation.

- **Charger function for Milwaukee 18 V batteries.**
- **Bluetooth function with 30 m range.**
- **12 V USB output for charging mobile phones or operation of portable audio devices.**
- **Operation with Milwaukee 18 V batteries or with 230 V mains voltage.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes mains cable, 2 back-up batteries, AUX connection cable, without batteries.

Technical description

Battery voltage	18 V
Height	381 mm
Length	304 mm

Weight	7.7 kg
Manufacturer's designation	M18RC-0
Width	304 mm
Interface	Bluetooth interface
Interface	USB interface
Number of rechargeable batteries contained	0
IP Index of Protection	IP 54
Power supply	Rechargeable battery-powered
Power supply	Mains operated
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Radio

Accessories

Battery charger Type M1218C	073840 M1218C
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218FC	073840 M1218FC